

25mm Diameter, 0° AOI, Hot Mirror



Hot Mirrors

Stock #43-842 3-4 DAYS

⊖ 1 ⊕

€46,00

ADD TO CART

Qty 1-9

€46,00

Qty 10+

€40,40

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0.00

Coating:
Hot Mirror, 0°

Diameter (mm):
25.00 ±0.25

Substrate:  BOROFLOAT®
Reflection (%) : >95, 750 - 1150nm
Surface Quality : 80-50
Thickness (mm) : 3.30
Transmission (%) : >90, 425 - 675nm
Type : Shortpass Filter
Coating Specification : Surface 1: 0° Hot Mirror Surface 2: None
Wavelength Range (nm) : 425 - 1150
Surface Flatness (P-V) : 4 - 6λ
Coating Type : Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant