

TECHSPEC® 25mm Dia., Deep UV (DUV) Mirror



Precision Ultraviolet Mirrors

Stock **#48-568** ☒ In Stock

⊖ 1 ⊕ **€260,00**

ADD TO CART

Qty 1-5
€260,00

Qty 6+
€208,00

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Surface Flatness (P-V):
λ/10

Substrate: ☐

Fused Silica (Coming 7980)	
Back Surface:	Ground
Surface Quality:	10-5
Coating Specification:	R _{avg} >88% @ 190 - 195nm R _{avg} >85% @ 200 - 600nm
Coating:	Enhanced Aluminum (190-600nm)
Coating Type:	Metal
Angle of Incidence (°):	0
Clear Aperture (%):	90
Design Wavelength DWL (nm):	190
Parallelism (arcmin):	<3
Thickness (mm):	6.00 ±0.2
Thickness Tolerance (mm):	±0.2
Type:	Flat Mirror
Wavelength Range (nm):	190 - 600
Vacuum Compatibility:	10 ⁻⁷ Torr

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View