

TECHSPEC®

25mm H x 50mm L x 100mm FL MgF₂ Coated, Illumination Grade PCX Cylinder Lens



Stock #48-366 3-4 DAYS

- 1 + **€120,00**

ADD TO CART

Qty 1-5
€120,00

Qty 6+
€96,00

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate: ☐
[N-BK7](#)

f/#:

4
Numerical Aperture NA: 0.13
Coating: MgF ₂ (400-700nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): 97.98
Center Thickness CT (mm): 3.16
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 1.63
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.85
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 10 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant