

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm H X 50mm L X 100mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #46-023 [CONTACT US](#)

-

1

+

 €110,00

ADD TO CART

Qty 1-5

€110,00

Qty 6+

€88,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate:
[N-BK7](#)

f/#:
4

Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 97.98
Center Thickness CT (mm): 3.16
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 1.63
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.85
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View