

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm H X 50mm L X -50mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #68-064 3-4 DAYS



1



€108,00

ADD TO CART

Qty 1-5

€108,00

Qty 6+

€86,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-50.00

Substrate: ☐
[N-BK7](#)

Coating:
Uncoated

Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -52.64
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 7.06
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -25.84
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View