

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm Uncoated Dove Prism



Stock #45-403 3-4 DAYS



1



€191,00

ADD TO CART

Qty 1-5

€191,00

Qty 6+

€171,90

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[N-BK7](#)

Height (mm):

25.0

Length (mm): 103.18
Surface Quality: 60-40
Type: Dove Prism
Dimensional Tolerance (mm): ±0.13 Legs, ±0.25 Length
Angle Tolerance (arcmin): 2.00
Bevel: Protective bevel as needed
Image Orientation: Left-Handed
Ray Deviation (°): 0
Surface Flatness (P-V): λ/8 (Entrance and Exit Faces)

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View