

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

2.5" X 2.5" , 2.0" FL, Aspheric Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock #43-025 3-4 DAYS



1



€36,00

ADD TO CART

Qty 1-10

€36,00

Qty 11+

€31,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
50.80

Substrate: ☐
Acrylic

Coating:
Uncoated

Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 2.5 x2.5
Dimensions (mm): 63.5 x63.5
Effective Diameter (inches): 2.0
Effective Focal Length EFL (inches): 2.00
Groove Density (grooves/inch): 110.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View