

TECHSPEC®

# 3.0 OD 50mm Diameter UV-VIS ND Filter



Stock **#62-671** 3-4 DAYS

-

1

+

€202,00

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €202,00 |

|         |
|---------|
| Qty 6+  |
| €161,60 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



|                                                                                           |
|-------------------------------------------------------------------------------------------|
| <b>Diameter (mm):</b><br>50.00 +0.00/-0.20                                                |
| <b>Optical Density OD (Average):</b><br>3.0                                               |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980) |

|                                                     |
|-----------------------------------------------------|
| <b>Coating:</b><br>Metallic Based ND                |
| <b>Surface Quality:</b><br>40-20                    |
| <b>Thickness (mm):</b><br>5.00                      |
| <b>Thickness Tolerance (mm):</b><br>±0.10           |
| <b>Transmission (%):</b><br>0.1                     |
| <b>Type:</b><br>Neutral Density Filter              |
| <b>Blocking Wavelength Range (nm):</b><br>250 - 700 |
| <b>Clear Aperture (%):</b><br>80.00                 |
| <b>Transmitted Wavefront, P-V:</b><br>λ/4           |
| <b>Optical Density Tolerance (%):</b><br>±10        |
| <b>Parallelism (arcsec):</b><br><5                  |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |

---