

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

307nm CWL, 10nm FWHM, 50mm Mounted Diameter



Stock #67-885 3-4 DAYS



1



€486,00

ADD TO CART

Qty 1-9

€486,00

Qty 10+

€436,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.25

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm): 45.0
Center Wavelength CWL (nm): 307.00 +3.0/-0.0
Center Wavelength CWL Tolerance (nm): +3.0/-0.0
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): >15
Operating Temperature (°C): -50 to +50
Coating: Traditional Coated
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: Zn Emission Line
Blocking Wavelength Range (nm): 200 - 10000
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant