

TECHSPEC® 30mm, 40mm Radius, English Goniometer



30mm, 40mm Radius, English Goniometer

Stock **#66-520** 3-4 DAYS



1



€365,00

ADD TO CART

Qty 1-2

€365,00

Qty 3+

€318,30

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:
English

Stage Size (mm): 30 x 30
Travel (°): ±15
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 2
Mounting Threads: (1) 1/4-20, (8) 2-56
Radius R (mm): 40
Resolution (arcmin): 5
Stage Size (inches): 1.18 x 1.18
Weight (kg): 0.15

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant