


[All Products](#) / [Optomechanics](#) / [Manual Translation Stages and Slides](#) / [Manual Stages and Slides](#) / [Goniometers](#)

[See all 18 Products in Family](#)

TECHSPEC® 30mm, 82mm Radius, English Goniometer



+1

Stock #66-522 3-4 DAYS

⊖ 1 ⊕

€457,00

[ADD TO CART](#)

Qty 1-2	
€457,00	

€457,00

Qty 3+	
€399,20	

€399,20

Volume Pricing [Request Quote](#)

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type: English
Stage Size (mm): 30 x 30
Travel (°): ±7.5
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 2
Mounting Threads: (1) ¼-20, (8) 2-56
Radius R (mm): 82
Resolution (arcmin): 10
Stage Size (inches): 1.18 x 1.18
Weight (kg): 0.15

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant