

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



30mm Precision Stage, English Dovetail Carrier

Stock #12-508 3-4 DAYS



1



€107,00

ADD TO CART

Qty 1-9

€107,00

Qty 10+

€94,40

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive:
Manual

Type: English
Length (inches): 1.18
Length (mm): 30.00
Construction: Black Anodized Aluminum
Mounting Threads: (8) 2-56, (1) 1/4-20
Note: Carrier

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
