

TECHSPEC® 30mm, Center Drive, Standard Top, 0.25" Travel, Metric Micrometer



Stock #83-505 3-4 DAYS

- 1 + **€362,00**

ADD TO CART

Qty 1-2
€362,00
Qty 3+
€315,70
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Metric Micrometer

Drive Orientation:

Center Drive
Type: Metric
Stage Size (mm): 30 x 30
Travel (mm): 6.5
Center Hole: M6 x 1
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 3
Mounting Threads: (1) M6 x 1, (6) M2 x 0.4
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
