

**TECHSPEC® 30mm, Center Drive, Thru-Hole, 0.25" Travel, English Micrometer**



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Thru-Hole Model)



Stock **#83-507** 3-4 DAYS

⊖ 1 ⊕

€392,00

ADD TO CART

Qty 1-2

€392,00

Qty 3+

€342,30

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:  
Linear (X)

Guide System:  
Crossed Roller Bearing

|                                                    |
|----------------------------------------------------|
| <b>Type of Drive:</b><br>English Micrometer        |
| <b>Drive Orientation:</b><br>Center Drive          |
| <b>Type:</b><br>English                            |
| <b>Stage Size (mm):</b><br>30 x30                  |
| <b>Travel (inches):</b><br>0.25                    |
| <b>Center Hole:</b><br>5/16"-24                    |
| <b>Construction:</b><br>Aluminium Stage            |
| <b>Leadscrew Pitch (mm):</b><br>0.635              |
| <b>Load Capacity (kg):</b><br>3                    |
| <b>Mounting Threads:</b><br>(1) 5/16"-24, (6) 2-56 |
| <b>Stage Size (inches):</b><br>1.18 x 1.18         |
| <b>Straight Line Accuracy (µm):</b><br>2           |
| <b>Pitch (arcsec):</b><br>30                       |
| <b>Yaw (arcsec):</b><br>25                         |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Contains SVHC(s)</a>      |