

30mm Dia. 405nm $\lambda/2$ Quartz Waveplate Zero Order



Stock **#83-930** 3-4 DAYS

- 1 + **€640,00**

ADD TO CART

Qty 1-5
€640,00

Qty 6+
€520,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
23.0

Coating:
Laser V-Coat (405nm)

Design Wavelength DWL (nm):
405

Diameter (mm):

30.00 +0.00/-0.25
Substrate: Crystal Quartz
Retardance: λ/2
Surface Quality: 10-5
Thickness (mm): 6.00 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/8 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View