

**TECHSPEC®** 30mm Dia Silver, 4-6λ Mirror



Stock **#89-487** 3-4 DAYS

- 1 + **€36,00**

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €36,00  |

|        |
|--------|
| Qty 6+ |
| €27,50 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Diameter (mm):**  
30.00 ±0.25

**Surface Flatness (P-V):**  
4 - 6λ

**Substrate:** ☐  
Float Glass

**Surface Quality:**

|                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------|
| 60-40                                                                                                            |
| <b>Dimensional Tolerance (mm):</b><br>±0.25                                                                      |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >98% @ 450 - 2000nm<br>R <sub>avg</sub> >98% @ 2000 - 10,000nm |
| <b>Coating:</b><br>Protected Silver (450-10000nm)                                                                |
| <b>Coating Type:</b><br>Metal                                                                                    |
| <b>Clear Aperture CA (mm):</b><br>28.50                                                                          |
| <b>Edges:</b><br>Ground, 0.5mm Maximum Edge Chip                                                                 |
| <b>Thickness (mm):</b><br>3.00 nominal                                                                           |
| <b>Type:</b><br>Flat Mirror                                                                                      |
| <b>Wavelength Range (nm):</b><br>450 - 10000                                                                     |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>0.5 J/cm <sup>2</sup> @ 532nm & 1064nm, 10ns     |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |