

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #83-506 3-4 DAYS



1



€362,00

ADD TO CART

Qty 1-2

€362,00

Qty 3+

€315,70

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:  
Linear (X)

Guide System:  
Crossed Roller Bearing

Type of Drive:

|                                                      |
|------------------------------------------------------|
| Metric Micrometer                                    |
| <b>Drive Orientation:</b><br>Side Drive              |
| <b>Type:</b><br>Metric                               |
| <b>Stage Size (mm):</b><br>30 x 30                   |
| <b>Travel (mm):</b><br>6.5                           |
| <b>Center Hole:</b><br>M6 x 1                        |
| <b>Construction:</b><br>Aluminium Stage              |
| <b>Leadscrew Pitch (mm):</b><br>0.5                  |
| <b>Load Capacity (kg):</b><br>3                      |
| <b>Mounting Threads:</b><br>(1) M6 x 1, (6) M2 x 0.4 |
| <b>Stage Size (inches):</b><br>1.18 x 1.18           |
| <b>Straight Line Accuracy (µm):</b><br>2             |
| <b>Pitch (arcsec):</b><br>30                         |
| <b>Yaw (arcsec):</b><br>25                           |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Contains SVHC(s)</a>      |