

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 30R/70T NIR, C-Mounted Plate Beamsplitter



Stock #49-687 [CONTACT US](#)



1



€295,00

ADD TO CART

Qty 1-4

€295,00

Qty 5+

€259,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating Specification:

Surface 2: Multi-Layer Anti-Reflection for Near-Infrared Region

Construction:

Plate

Dimensional Tolerance (mm):

+0.0/-0.25

|                                                                     |
|---------------------------------------------------------------------|
| <b>Extension Length (mm):</b><br>38.0                               |
| <b>Housing:</b><br>Black Anodized Aluminum                          |
| <b>Housing Dimension:</b><br>38 x 38 x 50                           |
| <b>Mount:</b><br>C-Mount Enclosure                                  |
| <b>Reflection/Transmission Ratio (R/T):</b><br>30/70                |
| <b>Reflection/Transmission Tolerance (%):</b><br>±5                 |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a> |
| <b>Surface Flatness (P-V):</b><br>1λ                                |
| <b>Surface Quality:</b><br>60-40                                    |
| <b>Thread Type:</b><br>C-Mount (1" x 32 TPI)                        |
| <b>Type:</b><br>Standard Beamsplitter                               |
| <b>Wavelength Range (nm):</b><br>700 - 1100                         |
| <b>Beamsplitter Included:</b><br><a href="#">#49-753</a>            |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |