

3.1" High Brightness LED Diffuselite, 625nm

See More by [Advanced Illumination](#)



Advanced Illumination Diffuselite LED Illuminators

Stock **#88-499** [CONTACT US](#)

- 1 +

€1.056,00

ADD TO CART

Qty 1+

€1.056,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Height (mm):
7.00

Model Number:
DL194-625-IC

Operating Temperature (°C): 0 to 65
Outer Diameter (mm): 133.4
Wavelength (nm): 625.00
Working Distance (mm): 13 - 50
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10 Edge to Edge (Dependent on Working Distance)
Number of LEDs: 12.00
Number of Channels: 1.00
Field Coverage (mm): 89.00
Maximum Trigger Frequency (Hz): 30.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Diffuse
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)