

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 35 X 35mm 20R/80T, VIS Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock #68-373 3-4 DAYS



1



€198,00

ADD TO CART

Qty 1-5

€198,00

Qty 6+

€158,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

45

Clear Aperture (%):

>85

Coating Specification:

Surface 1: 20/80 ±5% @ 550nm, ±10% @ 400 -

700nm Surface 2: AR $R_{avg} \leq 1\%$, $R_{abs} \leq 2\%$ @ 400 - 700nm
Construction: Plate
Dimensions (mm): 35.0 x 35.0 +0.0/-0.25
Edges: Cut with 0.25mm maximum edge chip
Note: Beamsplitter-coated side is marked with a black dot
Parallelism (arcmin): ≤ 3
Reflection/Transmission Ratio (R/T): 20/80
Substrate: ☐ N-BK7
Surface Flatness (P-V): 1 λ per inch
Surface Quality: 60-40
Thickness (mm): 3.00 $\pm$ 0.25
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant