

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

35.0mm FL, NO IR-Cut Filter, 1/2, Micro Video Lens



Stock #59-780 3-4 DAYS

- 1 + €70,00

ADD TO CART

Qty 1-49

€70,00

Qty 50+

€55,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
23.40

Filter Thread:
M12 x 0.50

Maximum Diameter (mm):
25.0

Maximum Image Circle (mm):

11.00
Horizontal Field of View @ Max Sensor Format: 13.6
Resolution, On-Axis: 160 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 100 lp/mm @ 20% Contrast
Resolution, Full Field: 80 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 35.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
Distortion (%): -1.10 @ Full Field
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
