

35mm Diameter x 26.2mm FL, Aspheric Condenser Lens



Stock **#43-988** ☐ In Stock

[Other Coating Options](#)

-

1

+

€56,00

ADD TO CART

Qty 1-10
€56,00

Qty 11+
€49,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
35.00 +0.0/-0.4

Effective Focal Length EFL (mm):
29.00

Numerical Aperture NA:
0.61

Back Focal Length BFL (mm): 16.30
Substrate: B270
Focal Length Tolerance (%): ±7
Coating: Uncoated
Centering (arcmin): ≤25
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 29.1
Edge Thickness ET (mm): 4.0
Center Thickness CT (mm): 13.90 ±0.25
f/#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 31.1
Radius R ₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View