

TECHSPEC® 35mm, f/11 Cw Series Fixed Focal Length Lens



35mm Focal Length



Stock **#15-660** 3-4 DAYS



1



€325,00

ADD TO CART

Qty 1+

€325,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Fixed

Length (mm):
59.68

Horizontal Field of View, 1/2" Sensor:
10.4°

Horizontal Field of View, 2/3" Sensor:

14.3°
Filter Thread: M34.0 x0.50 (Female)
Maximum Diameter (mm): 41.82
Outer Diameter (mm): 42
Horizontal Field of View, 1/3" Sensor: 7.8°
Maximum Rear Protrusion (mm): 1.82
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0117
Horizontal Field of View @ Max Sensor Format: 22.1mm - 14.3°
Number of Elements (Groups): 7 (6)
Note: C-Mount compatible with O-ring 25mm ID x2mm
Horizontal Field of View, 1/1.8" Sensor: 11.7°
Horizontal Field of View, 1/2.5" Sensor: 9.4°
Type: Fixed Focal Length Lens
Diameter (mm): 40.50
Focal Length FL (mm): 35.00
Primary Magnification PMAG: 0.341
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/11
Coating: 425 - 675nm BBAR
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 24.65
Horizontal Field of View, 1/4" Sensor: 5.9°
Object Space Principal Plane (mm): 25.81
Image Space Principal Plane (mm): -20.67
Field of View at Max Sensor Format: Horizontal: 14.3° Vertical: 10.8° Diagonal: 17.8°
Maximum Distortion (%): 0.17
Exit Pupil Position (mm): -21.87
Environmental Rating: IPX7 and IPX9K
Lens Wavelength Range: VIS
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

