

TECHSPEC® 36mm EFL Uncoated, UV-to-NIR Corrected Triplet



Stock **#65-029** 3-4 DAYS

- 1 + **€2.369,00**

ADD TO CART

Qty 1-5
€2.369,00
Qty 6+
€2.014,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
36.00

Focal Length Tolerance (%):
±0.5 @ 248nm

Back Focal Length BFL (mm):
24.98

Back Focal Length BFL from Housing (mm):

24.50
Clear Aperture CA (mm): 22.50
Substrate: ☐ CaF ₂ / Fused Silica / CaF ₂
Surface Quality: 60-40
f#: 1.6
Numerical Aperture NA: 0.31
Coating: Uncoated
Effective Focal Length EFL @ 248nm (mm): 36.00
Housing Diameter (mm): 30.00 ±0.05
Housing Length (mm): 27.00 ±0.05
Type: Achromatic Triplet Lens
Wavelength Range (nm): 193 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View