

370nm CWL, 10nm FWHM, 12.5mm Mounted Diameter



Stock #67-761 3-4 DAYS

⊖ 1 ⊕ **€155,00**

ADD TO CART

Qty 1-9
€155,00

Qty 10+
€139,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Diameter (mm): 12.50 +0.00/-0.25
Angle of Incidence (°): 0
Optical Density OD (Average): ≥4.0

Clear Aperture CA (mm): 9.0
Center Wavelength CWL (nm): 370.00 +3.0/-0.0
Center Wavelength CWL Tolerance (nm): +3.0/-0.0
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): >25
Operating Temperature (°C): -50 to +50
Coating: Traditional Coated
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: General Filtering
Blocking Wavelength Range (nm): 200 - 10000
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 5.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant