

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

3.74mm FL, High Resolution, 1/1.6, Micro Video Lens



Stock #11-323 3-4 DAYS

- 1 + €74,00

ADD TO CART

Qty 1-49

€74,00

Qty 50+

€57,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
24.04

Maximum Diameter (mm):
19.0

Maximum Image Circle (mm):
8.00

Horizontal Field of View @ Max Sensor Format:

Resolution, On-Axis:
100 lp/mm @61.7% Contrast

Resolution, 0.7 Field:
100 lp/mm @56.8% Contrast

Resolution, Full Field:
100 lp/mm @48.2% Contrast

Note:
High Resolution

TV Distortion (%):
-22.4

Type:
M12 Imaging Lens

Focal Length FL (mm):
3.74

Maximum Sensor Format:
1/2"

Working Distance (mm):
400 - ∞

Mount:
M12 x0.5 (S-Mount)

Aperture (f/#):
f/1.6

IR Cut Filter:
Yes

Lens Wavelength Range:
VIS (IR-Cut Filter)

Regulatory Compliance

Reach 205:
[Compliant](#)

Certificate of Conformance:
[View](#)