

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 35.0mm Dia. X 35.0mm FL, NIR I Coated, Plano-Convex Lens



Stock #38-382 3-4 DAYS

[Other Coating Options](#)

- 1 +

€55,00

ADD TO CART

Qty 1-9

€55,00

Qty 10+

€49,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
35.00 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                                                        |
|----------------------------------------------------------------------------------------|
| 35.00 @ 587.6nm                                                                        |
| <b>Back Focal Length BFL (mm):</b><br>30.52                                            |
| <b>Coating:</b><br>NIR I (600-1050nm)                                                  |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.5% @ 600 - 1050nm                 |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-SF11</a>                   |
| <b>Surface Quality:</b><br>40-20                                                       |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                  |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                            |
| <b>Focal Length Tolerance (%):</b><br>±1                                               |
| <b>Centering (arcmin):</b><br><1                                                       |
| <b>Center Thickness CT (mm):</b><br>8.00 ±0.10                                         |
| <b>Edge Thickness ET (mm):</b><br>1.70                                                 |
| <b>Radius R<sub>1</sub> (mm):</b><br>27.47                                             |
| <b>Clear Aperture CA (mm):</b><br>34                                                   |
| <b>f/#:</b><br>1.00                                                                    |
| <b>Numerical Aperture NA:</b><br>0.50                                                  |
| <b>Type:</b><br>Plano-Convex Lens                                                      |
| <b>Bevel:</b><br>Protective bevel as needed                                            |
| <b>Wavelength Range (nm):</b><br>600 - 1050                                            |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>7 J/cm² @ 1064nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |