

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

39mm Outer Dia., Zero Aperture, Burnished Steel Leaves



Zero Series

Stock #57-589 3-4 DAYS



1



€98,00

ADD TO CART

Qty 1-4

€98,00

Qty 5+

€86,40

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
22.0

Outer Diameter (mm):
39.0

Construction: Anodized Aluminum Alloy, Burnished Leaves
Full Angular Range of Lever (°): 99.00
Lever Diameter (mm): 3.00
Lever Length (mm): 12.00
Lever Position (mm): 2.50
Number of Leaves: Two sets of 7
Operating Temperature (°C): <250
Pin Thread & Pitch: M1.4 x 0.30mm
Thickness (mm): 5.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant