

TECHSPEC® 3mm, Alum. & AR Coated, N-SF11 Micro Right Angle Prism



N-SF11 Right Angle Prisms

Stock **#47-923** 3-4 DAYS

⊖ 1 ⊕ **€149,00**

ADD TO CART

Qty 1-5

€149,00

Qty 6+

€134,10

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
MgF₂ & Aluminized

Substrate: ☐
[N-SF11](#)

Surface Quality:
20-10

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.05
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 4.20
Length of Legs (mm): 3.00
Image Orientation: Left-Handed
Coating Specification: Legs: $R_{avg} \leq 1.75\%$ @ 400 - 700nm Hypotenuse: $R_{avg} > 85\%$ @ 400 - 700nm w/Black Overpaint
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): $\lambda/4$
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm^2 @ 532nm & 1064nm, 10ns Legs: 10 J/cm^2 @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant