

TECHSPEC® 3mm, Uncoated, N-SF11 Micro Right Angle Prism



N-SF11 Right Angle Prisms

Stock **#45-525** 3-4 DAYS



1



€121,00

ADD TO CART

Qty 1-5

€121,00

Qty 6+

€108,90

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Uncoated

Substrate: ☐
[N-SF11](#)

Surface Quality:
20-10

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.05
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 4.20
Length of Legs (mm): 3.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 2500
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View