

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

3mW 670nm, Laboratory Laser Diode



Stock #39-569 3-4 DAYS

1 €360,00

ADD TO CART

Qty 1+

€360,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Output Power (mW):
3 (±5%)

Wavelength (nm):
670.00

Wavelength Tolerance (nm):
±10

Power Supply:

110/240 VAC (included)
Power Requirement: 3.5 - 5 VDC, <50 mA
Beam Size at Nearest Focus (µm): 25
Note: Includes: Users Manual, Power Supply, Warning Label, and Focus Key
Beam Diameter (mm): 4 x2
Output Type: Free Space
Type of Laser: Diode
Beam Divergence (mrad): <0.5
Laser Class - CDRH: IIIa
Color: Red
Focus Range: 35mm - ∞

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
