

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 3" Dia, 12" FL Protected Gold, Spherical Mirror



Stock #49-619 CONTACT US

- 1 +

€321,00

ADD TO CART

Qty 1-9

€321,00

Qty 10+

€272,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±2

Surface Quality: 60-40

Surface Accuracy: λ/4
Diameter (inches): 3.0
Diameter (mm): 76.20 +1.0/-0
Diameter Tolerance (inches): +0.04/-0
Effective Focal Length EFL (inches): 12.00
Effective Focal Length EFL (mm): 304.80
Radius of Curvature (mm): 609.60
Aperture (f/#): f/4
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference:  0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant