

4" Fiber Optic Diffuse Axial Illuminators



4" Fiber Optic Diffuse Axial Illuminators (#53-381)



Stock **#53-381** 3-4 DAYS

- 1 +

€795,00

ADD TO CART

Qty 1+

€795,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Numerical Aperture NA:
0.55 nominal

Fiber Diameter (µm):
50 (0.002" nominal)

Construction:

Black Anodized Aluminum
Packing Fraction (%) : 83% nominal
Transmission Loss : 10% per ft. at 660nm
Type of Illumination : Fiber Optic Light Guide
Geometry : Diffuse Axial

Regulatory Compliance

Reach 174 : Compliant
RoHS : Not Compliant
Certificate of Conformance : View
