


In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

4 OD 12.5mm Dia, Absorptive ND Filter

See More by [Hoya](#)



Stock #36-272 [CONTACT US](#)



1



€31,00

ADD TO CART

Qty 1-10

€31,00

Qty 11+

€28,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Optical Density OD (Average):

4.00 ±0.2
Glass/Filter Number: Hoya ND-006
Substrate: ☐ ND Filter Glass
Coating: Uncoated
Index of Refraction n_d: 1.531
Surface Quality: 80-50
Transformation Temperature (°C): 542.00
Thickness (mm): 2.85
Thickness Tolerance (mm): ±0.5
Transmission (%): 0.01 (average)
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.1
Parallelism (mm): <0.02

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View