

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #13-629 [CONTACT US](#)



1



€629,00

ADD TO CART

Qty 1-4

€629,00

Qty 5+

€566,10

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Guide System:
Dovetail

Type of Drive:
Lead Screw

Type:

Metric
Stage Size (mm): 40 x 40
Travel (°): ±20
Construction: Brass Stage
Load Capacity (kg): 3
Mounting Threads: (1) M6 x 1.0, (4) M3 x 0.5, (4) M2 x 0.4
Radius R (mm): 31
Resolution (°): 0.2
Weight (kg): 0.25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant