

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #15-109 [CONTACT US](#)



1



€1.215,00

ADD TO CART

Qty 1+

€1.215,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
25.2 x 35.6

Filters Included :
Cut-off Wavelengths: [400nm](#), [450nm](#), [500nm](#), [550nm](#),
[600nm](#), [650nm](#), [700nm](#), [750nm](#)

Length (mm):
35.60

Type:
Shortpass Filter

Width (mm): 25.20
Number of Filters: 8
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
