

40° Diffusing Angle 25mm Dia., Fused Silica Holographic Diffuser



Holographic UV Diffusers

Stock **#48-511** 3-4 DAYS



1



€457,50

ADD TO CART

Qty 1+

€457,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°):
±4

Diffusing Angle (°):
40 (FWHM)

Clear Aperture CA (mm):
21.6 ±0.1

Diameter (mm):
25.00 ±0.1

Operating Temperature (°C):

-40 to +170
Substrate: Fused Silica (Corning 7980)
Transmission (%): Typical: 90
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Mounted
Mount Thickness (mm): 4.7 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant