

TECHSPEC® 40mm, 60mm Radius, English Goniometer



40mm, 60mm Radius, English Goniometer

Stock **#66-526** 3-4 DAYS



1



€492,00

ADD TO CART

Qty 1-2

€492,00

Qty 3+

€429,40

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:
English

Stage Size (mm): 40 x 40
Travel (°): ±10
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 3
Mounting Threads: (1) ¼-20, (4) 6-32, (8) 2-56
Radius R (mm): 60
Resolution (arcmin): 5
Stage Size (inches): 1.57 x 1.57
Weight (kg): 0.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
