

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 4.0mm Dia. X 10.0mm FL, NIR I Coated, Plano-Convex Lens



Stock #48-705 3-4 DAYS

[Other Coating Options](#)

1 €58,00

ADD TO CART

Qty 1-9
€58,00

Qty 10+
€52,25

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
4.00 +0.0/-0.025

Effective Focal Length EFL (mm):

10.00 @ 587.6nm
Back Focal Length BFL (mm): 8.92
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.64 ±0.05
Edge Thickness ET (mm): 1.24
Radius R₁ (mm): 5.19
Clear Aperture CA (mm): 3.6
f/#: 2.5
Numerical Aperture NA: 0.20
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant