

TECHSPEC®

4.0mm Dia. x 4.0mm FL, Uncoated, Plano-Convex Lens



Stock **#45-223** ☐ In Stock
[Other Coating Options](#)

-

1

+

€47,00

ADD TO CART

Qty 1-9
€47,00
Qty 10+
€42,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
4.00 +0.0/-0.025

Effective Focal Length EFL (mm):

4.00 @ 587.6nm
Back Focal Length BFL (mm): 3.06
Coating: Uncoated
Substrate: N-LASF44
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 1.70 ±0.05
Edge Thickness ET (mm): 1.00
Radius R₁ (mm): 3.21
Clear Aperture CA (mm): 3.6
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2300

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View