

TECHSPEC® 40mm, English Z-Stage



TECHSPEC® Vertical Translation Stages



Stock #66-498 3-4 DAYS

- 1 + €598,00

ADD TO CART

Qty 1-2

€598,00

Qty 3+

€522,80

Volume Pricing

[Request Quote](#)

1 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (Z)

Guide System:
Crossed Roller Bearing

Type of Drive: Lead Screw
Type: English
Stage Size (mm): 40 x 40
Travel (mm): 10
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 2
Mounting Threads: (1) 1/4-20, (4) 6-32, (8) 2-56
Stage Size (inches): 1.57 x 1.57
Straight Line Accuracy (µm): 3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant