

TECHSPEC® 40mm, Metric Micrometer Z-Stage



TECHSPEC® Vertical Translation Stages



Stock #66-501 3-4 DAYS

- 1 + €646,00

ADD TO CART

Qty 1-2

€646,00

Qty 3+

€562,70

Volume Pricing

[Request Quote](#)

1 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (Z)

Guide System:
Crossed Roller Bearing

Type of Drive: Metric Micrometer
Type: Metric
Stage Size (mm): 40 x 40
Travel (mm): 10
Center Hole: M6 x 1
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 2
Mounting Threads: (1) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 1.57 x 1.57
Straight Line Accuracy (µm): 3

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View