

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 40mm, Side Drive, Thru-Hole, Metric Stage



40mm, Side Drive, Thru-Hole Stage

Stock #66-423 3-4 DAYS



1



€354,00

ADD TO CART

Qty 1-2

€354,00

Qty 3+

€309,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Lead Screw

Drive Orientation: Side Drive
Type: Metric
Stage Size (mm): 40 x 40
Travel (mm): 13
Center Hole: M12 x 0.5
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 4
Mounting Threads: (1) M12 x 0.5, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 1.57 x 1.57
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
