

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

40X DIN Achromatic Finite Int'l Standard Objective



Stock #33-439 3-4 DAYS



1



€110,00

ADD TO CART

Qty 1+

€110,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):  
546

Field of View (mm):  
0.5

Focal Length FL (mm):  
4.00

Length excluding Threads (mm):  
44.50

Magnification:  
40X

|                                                                            |
|----------------------------------------------------------------------------|
| <div>Maximum Diameter (mm):<br/>25</div>                                   |
| <div>Numerical Aperture NA:<br/>0.65</div>                                 |
| <div>Mounting Threads:<br/>RMS / 20.32mm x36 TPI</div>                     |
| <div>Compatible Tube Lens Focal Length (mm):<br/>Focal Length: 160mm</div> |
| <div>Type:<br/>Achromatic</div>                                            |
| <div>Depth of Field (µm):<br/>1.89</div>                                   |
| <div>Field of View, 18 Diameter Field Eyepiece (mm):<br/>0.45</div>        |
| <div>Operating Temperature (°C):<br/>+10 to +40</div>                      |
| <div>Operating Humidity:<br/>Max 85% at 35°C with no condensation</div>    |
| <div>Working Distance (mm):<br/>0.6</div>                                  |
| <div>Weight (g):<br/>83</div>                                              |
| <div>Wavelength Range (nm):<br/>400 - 700</div>                            |
| <div>Style:<br/>Finite Conjugate</div>                                     |
| <div>Field Number (mm):<br/>20</div>                                       |
| <div>Parfocal Length (mm):<br/>45.1</div>                                  |
| <div>Immersion Liquid:<br/>N/A</div>                                       |

Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |