

40X DIN Achromatic Commercial Grade Objective



Stock #43-904 3-4 DAYS

⊖ 1 ⊕ **€130,00**

ADD TO CART

Qty 1+
€130,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
4.65

Length excluding Threads (mm):
45.80

Magnification:
40X

Maximum Diameter (mm):
24

Numerical Aperture NA:
0.65

Mounting Threads: 0.7965-36 TPI, 55° Whitworth
Type: Achromatic, Spring-Loaded
Operating Temperature (°C): 5 to 40
Storage Temperature (°C): -20 to 60
Working Distance (mm): 0.48
Style: Finite Conjugate
Parfocal Length (mm): 46.26
Immersion Liquid: N/A
Operating Relative Humidity: 45% to 85%

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View