

TECHSPEC® 4.22X Magnification, NIR I Coated, Mounted Anamorphic Prism Pair



#47-274 4.22X Magnification, NIR I Coated, Mounted Anamorphic Prism Pair

Stock **#47-274** 3-4 DAYS



1



€460,00

ADD TO CART

Qty 1-5

€460,00

Qty 6+

€414,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
NIR I (600-1050nm)

Angle Tolerance (arcmin):
3

Coating Specification:
R_{avg} ≤0.5% @ 600 - 1050nm

Design Wavelength DWL (nm): 830
Dimensional Tolerance (mm): +0.00/-0.10
Magnification: 4.22X
Mount: Mounted (Fixed Magnification)
Reflection at DWL (%): Average: <0.5
Substrate: ☐ N-SF11
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Type: Beam Shaping
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View