

25mm Max. Aperture, Iris Diaphragm



Stock **#40-997** 3-4 DAYS

⊖ 1 ⊕ **€93,00**

ADD TO CART

Qty 1-4
€93,00

Qty 5+
€82,40

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.2

Maximum Aperture (mm):
25.0

Outer Diameter (mm):

42.6
Construction: Brass Housing, Blue Tempered Steel Leaves
Lever Diameter (mm): 5.20
Lever Length (mm): 21.00
Number of Leaves: 10
Thickness (mm): 5.80

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)