

TECHSPEC®

4.5mm Dia. x 4.5mm FL, Uncoated, Plano-Convex Lens



Stock **#45-143** 3-4 DAYS
[Other Coating Options](#)

-

1

+

€47,00

ADD TO CART

Qty 1-9
€47,00
Qty 10+
€42,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
4.50 +0.0/-0.025

Effective Focal Length EFL (mm):

4.50 @ 587.6nm
Back Focal Length BFL (mm): 3.05
Coating: Uncoated
Substrate: ☐ N-LASF44
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 2.59 ±0.05
Edge Thickness ET (mm): 1.80
Radius R₁ (mm): 3.61
Clear Aperture CA (mm): 4.05
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2300

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View