

TECHSPEC® 4.5mm, f/5.6 Cr Series Fixed Focal Length Lens



4.5mm Cr Series Fixed Focal Length Lens

Stock **#37-401** 3-4 DAYS



1



€485,00

ADD TO CART

Qty 1+

€485,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Fixed

Length (mm):
32.13

Horizontal Field of View, 1/2" Sensor:
53.9mm - 69.4°

Filter Thread:
M58 x0.75 with required adapter [#87-425](#)

Weight (g):

89
Horizontal Field of View, 1/3" Sensor: 44.0mm - 59.2°
Maximum Image Circle (mm): 9.00
Horizontal Field of View @ Max Sensor Format: 72.0mm - 84.7°
Number of Elements (Groups): 7 (6)
Horizontal Field of View, 1/1.8" Sensor: 72.0mm - 84.7°
Front Thread: M40.0 x0.5 (Male)
Type: Fixed Focal Length Lens
Diameter (mm): 33.80
Focal Length FL (mm): 4.50
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 25 - ∞
Mount: C-Mount
Aperture (f/#): f/5.6
Coating: 425 - 675nm BBAR
Horizontal Field of View, 1/4" Sensor: 32.0mm - 45.2°
Lens Wavelength Range: VIS
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View