

## TECHSPEC® 45mm, Uncoated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock #32-533 3-4 DAYS

⊖ 1 ⊕ **€172,00**

**ADD TO CART**

Qty 1-5

€172,00

Qty 6+

€154,80

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:  
Uncoated

Substrate:   
[N-BK7](#)

Surface Quality:

60-40

**Type:**  
Right Angle Prism

**Dimensional Tolerance (mm):**  
±0.1

**Angle Tolerance (arcmin):**  
±2

**Bevel:**  
Protective bevel as needed

**Length of Hypotenuse (mm):**  
63.60

**Length of Legs (mm):**  
45.00

**Image Orientation:**  
Left-Handed

**Ray Deviation (°):**  
90

**Wavelength Range (nm):**  
350 - 2200

**Power (fringes) @ 632.8nm:**  
1.25

**Irregularity (fringes) @ 632.8nm:**  
0.50

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Reach 219:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---